



CIRCUITO	C1	C2	C3	C4	C5	C6	C7	C8	F5	F1	F2	F3	F4	F1	F2	F3	C9	C10	L1	L2	L3	L4			C11	EM 1	EM 2			ASCEN.	MORSETTI A	
DESTINAZIONE	MAGNETE PRINC. CONSOLLE	CONSOLLE INDIPEND.	FUTURA INSTALL.	SERBATOIO	CAMERA OSCURA	CDZ COMPUTERS	GENERI	ESTRATORI	CENT. ANTUM.	PRESE SERVIZIO	=	=	=	=	PREP. PATIENTE	SALA MAGNETE	=	SERV. BRUKER	ASCENSORE	LUCE	=	=	LUCE ASCENS.	=	=	MAGNETE BRUKER	EMERG.	=	FUTURA INSTALL.	=	ASCEN. OFF/ON	MORSETTI A DISPOSIZ. USI
CORRENTE (A)	80/100	8/63	=	44	12	232	36	4		15	18	=	=	=	4.5	=	=	20								28.5						
INTERRUTTORE	100	80	80	63	32	63	=	20		15	=	=	=	=	5	=	=	40	50A7	10	=	=	10			50	10	10				
POTENZA (W)	40.000	20.000		25.000	6.000	3.400	19.01	2000		3000	=	=	=	=	1.000	=	=		10.500				1			15.000	=	=				
SENSIBILITA'	0.03	=	=	0.6	=	=	=	=									0.03	0.03		=	=	0.03			0.03							
SEZIONE CAVI mm²	5 x 35	5 x 25	5 x 25	5 x 25	5 x 6	5 x 10	5 x	5 x 4		4 x 25	3 x 4	=	=	=	=	=	4 x 10	5 x 16	3 x 25	=	=	3 x 25			5 x 16	2 x 15	=					
TUBAZIONE	FMP Ø 50	=	=	FMP Ø 50	FMP Ø 32	FMP Ø 40	=	FMP Ø 32		FMP Ø 60	=	=	=	=	=	=		FMP Ø 40	FMP Ø 46	=	=				FMP Ø 40	FMP Ø 16	=					
N° MORSETTI	1 2 3 4	5 6 7 8	9 10 11 12	13 14 15 16	17 18 19 20	21 22 23 24	25 26 27	28 29 30 31	32 33 34 35	36 37 38	39 40	41 42	43 44	45 46	47 48 49 50	51 52	53 54 55 56	57 58 59 60	61 62	63 64	65 66	67 68	69 70 71 72	73 74	75 76	77 78	79 80					